

Fume Hood Survey Form

Southwest Solutions Group

The diagram shows a top-down view of a fume hood with various ports and components labeled for surveying. On the left side, from top to bottom, there are labels: Light Switch, Plugged (Air, Gas, Vac, Etc.), Plugged (Air, Gas, Vac, Etc.), Plugged (Air, Gas, Vac, Etc.), Plugged (Air, Gas, Vac, Etc.), Plugged (Air, Gas, Vac, Etc.), and Electrical (120VAC, GFI, Other). On the right side, from top to bottom, there are labels: System Indicator Light (Yes, No), (Fan Switch or Blank), Alarm (LOC500, LOC1000), Plugged (Air, Gas, Vac, Etc.), Plugged (Air, Gas, Vac, Etc.), Plugged (Cold Water), and Electrical (120VAC, GFI, Other). Below the diagram, there are sections for Liner Options, Pre-Pipe, and Length.

Liner Options (pick only one)

- Chem Resin (Standard)
- Stainless Steel 304
- Phenolic Resin
- Polypro

Pre-Pipe (pick one if needed)

- Pre-pipe Up
- Pre-Pipe Down

Length: (pick one only)

48" 60" 72" 96"

Add on Options

<p>Hood Cabinets (Pick one or two for 48", pick two for 60" & up)</p> <ul style="list-style-type: none"> <input type="checkbox"/> None (Base Supplied By Customer) <input type="checkbox"/> Standard Hood Base <input type="checkbox"/> Acid Storage <input type="checkbox"/> Flammable Storage <p>Interior Lighting (pick only one)</p> <ul style="list-style-type: none"> <input type="checkbox"/> Fluorescent (T-8) <input type="checkbox"/> Led Lighting <input type="checkbox"/> Explosion Proof 	<p>Hood Sash (pick only one)</p> <ul style="list-style-type: none"> <input type="checkbox"/> Combo Horizontal/Vertical (Standard) <input type="checkbox"/> Horizontal Only <p>Miscellaneous Options</p> <ul style="list-style-type: none"> <input type="checkbox"/> Tissue Screen <input type="checkbox"/> Gravity Sash Stop <input type="checkbox"/> Distillation Rack <input type="checkbox"/> Additional Electrical
--	--

Other Options Available Upon Request